

High Power
Durability
Digital Communication



XGT
40V Li-ion max **XGT X2**
80V max



Comfort/Lifestyle

Cordless Kettle
KT001G

40V max



Water Tank Capacity 800 mL
Dimensions 233 x 322 x 307 mm
(L x W x H) (9-1/8 x 12-5/8 x 12-1/8")
Net weight 2.8 - 5.9 kg (6.2 - 13.0 lbs.)

Cordless Cooler & Warmer Box

CW001G

40V max
18V



CW002G

40V max
18V



CW003G

40V max
18V



| | CW001G | CW002G | CW003G |
|------------------|---|---|---|
| Capacity | 20 L (5.3 gal) | 50 L (13.2 gal) | 7 L (1.8 gal) |
| Cooling Capacity | -18 / -15 / -10 / -5 / 0 / 5 / 10°C (0 / 5 / 15 / 25 / 30 / 40 / 50°F) | -18 / -15 / -10 / -5 / 0 / 5 / 10°C (0 / 5 / 15 / 25 / 30 / 40 / 50°F) | -18 / -15 / -10 / -5 / 0 / 5 / 10°C (0 / 5 / 15 / 25 / 30 / 40 / 50°F) |
| Warming Capacity | 30 / 35 / 40 / 45 / 50 / 55 / 60°C (85 / 95 / 105 / 115 / 120 / 130 / 140°F) | 30 / 35 / 40 / 45 / 50 / 55 / 60°C (85 / 95 / 105 / 115 / 120 / 130 / 140°F) | 30 / 35 / 40 / 45 / 50 / 55 / 60°C (85 / 95 / 105 / 115 / 120 / 130 / 140°F) |
| Dimensions | 663 x 341 x 372 mm (L x W x H) (26-1/8 x 13-3/8 x 14-5/8") | 867 x 465 x 476 mm (34-1/8 x 18-1/4 x 18-3/4") | 456 x 245 x 308 mm (18 x 9-5/8 x 12-1/8") |
| Net weight | 13.8 - 17.3 kg (30.4 - 38.1 lbs.) | 25.6 - 29.0 kg (56.4 - 63.9 lbs.) | 7.9 - 9.4 kg (17.4 - 20.7 lbs.) |

Charging Time

| | Fast Charging | | | |
|------------------|---------------|---------|---------|--------|
| | DC40RA | DC40RB | DC40RC | DC40WA |
| *1 BL4020 2.0Ah | 22 min | 30 min | 110 min | |
| *1 BL4025 2.5Ah | 28 min | 38 min | 130 min | |
| *1 BL4040 4.0Ah | 45 min | 67 min | 210 min | |
| *1 BL4050F 5.0Ah | 50 min | 85 min | 260 min | |
| *1 BL4080F 8.0Ah | 76 min | 170 min | 420 min | |

*1 Recommended battery

Cordless Microwave

MW001G

| | |
|--|--|
| Useful cavity dimensions (W x D x H) | 255 x 241 x 120 mm (10 x 9-1/2 x 4-3/4") |
| Cavity capacity | 8 L |
| Microwave power | High / Low: 500 / 350 W |
| Operating frequency | 2,450 MHz |
| Continuous run time on full battery charge | 350 / 500 W, w/ BL4020 x2: 11 / 6 min. 350 / 500 W, w/ BL4025 x2: 14 / 8 min. 350 / 500 W, w/ BL4040 x2: 21 / 15 min. 350 / 500 W, w/ BL4050F x2: 30 / 22 min. 350 / 500 W, w/ BL4080F x2: 48 / 35 min. 350 / 500 W, w/ PDC1200: 113 / 84 min. |
| Dimensions (L x W x H) | w/o Battery: 318 x 343 x 338 mm (12-1/2 x 13-1/2 x 13-1/4") w/ BL4020 / BL4025: 366 x 343 x 338 mm (14-3/8 x 13-1/2 x 13-1/4") w/ BL4040: 372 x 343 x 338 mm (14-5/8 x 13-1/2 x 13-1/4") w/ BL4050F: 393 x 343 x 338 mm (15-1/2 x 13-1/2 x 13-1/4") w/ BL4080F: 412 x 343 x 338 mm (16-1/4 x 13-1/2 x 13-1/4") |
| Net weight | w/o Battery: 8.9 kg (19.6 lbs.) w/ Battery: 9.5-12.7 kg (20.9-28.0 lbs.) |

Not covered by EPTA-Procedure / Specifications may differ from country to country.

Makita Corporation


3-11-8 Sumiyoshi-cho, Anjo, Aichi, 446-8502 Japan

PRINTED IN JAPAN 202302


Microwave power
500/350 w

Cavity capacity
8 L

Popular size food container can be heated.



Control panel



Easy to clean up and maintain

Easy to clean flat cavity plate



Continuous heating time on a full battery charge (approx)

500w: 35 min*

Battery: BL4080F x2



* This is the total time of repeated maximum 8-minute continuous heating at 500W in temporary boost mode

| Continuous heating time on a full battery charge (approx) | | | | | | | |
|---|-----------|-----------|-----------|------------|------------|---------|---------|
| Battery | BL4020 x2 | BL4025 x2 | BL4040 x2 | BL4050F x2 | BL4080F x2 | PDC1200 | |
| Microwave power | 350W | 11 min | 14 min | 21 min | 30 min | 48 min | 113 min |
| | 500W | 6 min | 8 min | 15 min | 22 min | 35 min | 84 min |



| Approx number of times an item can be heated With two fully charged BL4040 batteries | |
|---|--|
| food container of chilled items 5 times | mug of drink (200mL) 8 times |



Three user-oriented functions

1. Stops heating promptly and automatically when tilted.

Does not heat while being tilted for increased relief even in the case of tipping over.



2. Stops heating promptly and automatically when the door is opened during heating.



3. Reminder beep for items left in the cavity

If the microwave door is not opened for 1 minute after heating, a sequence of 3 short beeps sounds every 1 minute for 2 minutes, notifying user of items left in the microwave.



Internal cavity light

Lights up when the door is opened and during heating.

Tempered door glass

- Hard-to-break
- The inside of cavity can be checked during heating.
- Left-hinged side opening door

USB output port

- 1 port (Type A for DC5V / 2.4A)
- With rubber cap for reduced chance of damage to terminal



Excellent portability

- Easy-to-carry compact design yet with proper cavity dimensions where popular size food container can be heated
- Large retractable carrying handle



Accessories

Shoulder belt set
Part No. 196817-8

