



Cordless Flashlight ML006G / DML816



XGT
40V LITHIUM-ION
max

18V
LITHIUM-ION



**Max luminous flux:
500 lm**



ML006G

XGT
40V LITHIUM-ION
max

DML816

18V
LITHIUM-ION

14.4V
LITHIUM-ION

**Continuous run time (approx)
on a full battery charge**

ML006G

51 h

Battery: BL4025
Low mode

DML816


75 h

Battery: BL1860B
Low mode



Max luminous flux
500 lm

Rotatable and foldable light head



Foldable light head **Rotatable light head**
(90° right and 180° left)

Can be used as a compact stationary lamp with the light head swivelled and folded fully.

ML006G
40V LITHIUM-ION max

DML816
18V LITHIUM-ION
40V LITHIUM-ION max



Light diffusing lens
• softens the light of LED to reduce glare.
• provides widespread illumination.

Large hook
Light head is rotatable with the flashlight hanging down.

Retractable back into the upper portion of handle

Battery capacity warning
This system warns user by reducing the number of ON LED lights down to 1 before the battery is empty.

3-stage brightness adjustment
High → Medium → Low → OFF

Accessories ● Standard equipment

Lamp shade

Part No. GM00001326 ●
By attaching to the Cordless Flashlight ML006G / DML816, the irradiation range is widened and the glare of the light source is reduced.



without Lamp shade with Lamp shade

Shoulder hook set

Part No. GM00001288 ●



Charging Time

	Fast Charging			Fast Charging	
	DC40RA	DC40RC		DC18RC	DC18SD
BL4020 2.0Ah	22 min	30 min	BL1815N 1.5Ah	15 min	30 min
BL4025 2.5Ah	28 min	38 min	BL1820B 2.0Ah	24 min	45 min
BL4040 4.0Ah	45 min	67 min	BL1830B 3.0Ah	22 min	60 min
BL4050F 5.0Ah	50 min	85 min	BL1840B 4.0Ah	36 min	90 min
			BL1850B 5.0Ah	45 min	110 min
			BL1860B 6.0Ah	55 min	130 min

Cordless Flashlight

ML006GX / DML816X

	ML006G	DML816
Run Time (hrs)	Up to: 82 (Low mode, with BL4040)	Up to: 75 (Low mode, with BL1860B)
Illuminance (at 0.5m from the light source)	High/ Medium/ Low: 800 / 400 / 180 lx	High/ Medium/ Low: 800 / 400 / 180 lx
Luminous Flux	High/ Medium/ Low: 500 / 250 / 100 lm	High/ Medium/ Low: 500 / 250 / 100 lm
Dimensions (L x W x H)	w/ BL4040: 275 - 408 x 85 x 148 mm (10-7/8 - 16 x 3-3/8 x 5-7/8")	w/ BL1830B / BL1840B / BL1850B / BL1860B: 267 - 400 x 79 x 127 mm (10-1/2 - 15-3/4 x 3-1/8 x 5")
Net weight	1.1 - 1.7 kg (2.4 - 3.8 lbs.)	0.70 - 1.1 kg (1.5 - 2.4 lbs.)

ML006GX/DML816X: Battery & charger not include

Standard Equipment: Shoulder hook (GM00001288), lamp shade (GM00001326)

not covered by EPTA-Procedure
Items of standard equipment and specifications may vary by country or area.

A4-062023-1

CÔNG TY TNHH MAKITA VIỆT NAM

Kho 4-5-6, Block 16, 18L12 Đường số 3, KCN VSP, P. Hòa Phú, TP. Thủ Đức, Bình Dương
ĐT: 0274 362 8338 - Fax: 0274 362 8339 - Website: www.makita.com.vn

CHI NHÁNH CTY TNHH MAKITA VN TẠI MIỀN BẮC
Khu 5, Số 1, Đường Số 6, KCN - BT - DV VSP, Bắc Ninh, P. Phú Chân, TP. Từ Sơn, T. Bắc Ninh.
ĐT: 0222 376 5942 Fax: 0222 376 5941

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG CHI NHÁNH HÀ NỘI
65 Trường Chinh, P. Phương Liệt, Q. Thanh Xuân, TP. Hà Nội.
ĐT: 0243 202 2385

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG CHI NHÁNH ĐÀ NẴNG
102 Trần Nữ Vương, P. Hải Châu 2, Q. Hải Châu, TP. Đà Nẵng.
ĐT: 0236 352 5078 / 0236 352 5179 Fax: 0236 352 5479

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG CHI NHÁNH CẦN THƠ
386 Võ Văn Kiệt, Khu Vực 5, P. An Thới, Q. Bình Thủy, TP. Cần Thơ.
ĐT: 0292 389 4358 Fax: 0292 389 4359

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG CHI NHÁNH BUỒN MA THUỘT
S8 Lê Đức Thọ, P. Thống Nhất, TP. Buon Ma Thuột, T. Đắk Lắk.
ĐT: 0262 355 4556 Fax: 0262 355 4557

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG CHI NHÁNH HẢI PHÒNG
Số 01 Lũy Đái, Dự án Hoàng Huy Riverside, P. Thượng Lý, Q. Hồng Bàng, TP. Hải Phòng.
ĐT: 0225 883 1529

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG CHI NHÁNH NHA TRANG
Là 3636 đường B6, Khu đô thị Vinh Diêm Trung, Xã Vinh Ngọc, TP. Nha Trang, T. Khánh Hòa
ĐT: 0258 220 0039

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG CHI NHÁNH HỒ CHÍ MINH
Số 12 Trịnh Văn Căn, P. Cầu Ông Lãnh, Q. 1, TP. Hồ Chí Minh.
ĐT: 0283 821 5191