



# Cordless Bar Light ML012G / DML818



**XGT**  
**40V L<sup>+</sup>ION**  
**max**

**18V**  
**LITHIUM-ION**



photo: ML012G



photo: ML012G



photo: DML818

Continuous use  
on a full battery charge

**ML012G**

High / Medium / Low

**4.5 / 9.5 / 20h**

Battery: BL4025 / F

**DML818**

High / Medium / Low

**4 / 9.5 / 19h**

Battery: BL1850B

**ML012G**



**DML818**



## Bar type light for wide area illumination

For wide area illumination, we use a long bar type light consisting of two LED light bars, each of which is covered with a light-diffusing plastic lens.

### Foldable

- LED light bar section can be folded in half, allowing for double-sided illumination when folded.
- Compact for transportation or storage




### Illuminating angle adjustment by rotating LED light bar

By rotating LED light bar clockwise maximum 90 degrees or counterclockwise maximum 180 degrees, user can adjust the illuminating angle to 7 angles.



### Telescopic hook

- Clip on each end of Telescopic hook holds the LED light bar section securely.
- Telescopic hook allows user to attach the appliance to the hood, back door and more of vehicles, making it ideal for use as a worklight in automotive workshops.



### Illuminating angle adjustment with Telescopic hook attached



#### Top hook

This durable metal hook allows for use as a hanging worklight.

#### Hand strap

Supplied hand strap allows for use as a hanging worklight.


#### 3 Strap holes



#### Main power / Brightness switch

High → Med → Low → OFF

#### Illumination mode selection switch



- 1 All 42 LEDs on
- 2 24 LEDs on LEDs of lower light bar only
- 3 18 LEDs on LEDs of upper light bar only



ML012G

DML818

Max luminous flux  
**1,700 lm**  
with all 42 LEDs on

photo: ML012G

### Continuous use Illuminating with both lower and upper LED light bars (with all 42 LEDs on)

Model No.	ML012G					DML818					
	40V max					18V					
Battery	BL4020	BL4025/F	BL4040/F	BL4050F	BL4080F	BL1815N	BL1820B	BL1830B	BL1840B	BL1850B	BL1860B
Brightness setting	3.5 h	4.5 h	7.0 h	8.5 h	14 h	1.3 h	1.7 h	2.4 h	3.0 h	4.0 h	5.0 h
High (1,700 lm)	3.5 h	4.5 h	7.0 h	8.5 h	14 h	1.3 h	1.7 h	2.4 h	3.0 h	4.0 h	5.0 h
Medium (800 lm)	7.5 h	9.5 h	15 h	19 h	31 h	2.8 h	3.5 h	5.0 h	7.0 h	9.5 h	11 h
Low (400 lm)	16 h	20 h	32 h	40 h	65 h	5.5 h	7.5 h	10 h	15 h	19 h	23 h

## Charging Time

	Fast Charging		Standard Charging	
	DC40RA	DC40RB	DC40RC	DC40WA
BL4020 2.0Ah	22 min	30 min	110 min	
BL4025/F 2.5Ah	28 min	38 min	130 min	
BL4040/F 4.0Ah	45 min	67 min	210 min	
BL4050F 5.0Ah	50 min	85 min	260 min	
BL4080F 8.0Ah	76 min	170 min	420 min	

	Fast Charging		Standard Charging	
	DC18RC	DC18SD		
BL1815N 1.5Ah	15 min	30 min		
BL1820B 2.0Ah	24 min	45 min		
BL1830B 3.0Ah	22 min	60 min		
BL1840B 4.0Ah	36 min	90 min		
BL1850B 5.0Ah	45 min	110 min		
BL1860B 6.0Ah	55 min	130 min		

## Cordless Bar Light

### ML012G / DML818

Color temperature	Daylight white: 5,000 K
Luminous flux	High / Med. / Low: 1,700 / 800 / 400 lm
Illuminance	at 0.5m from the light source, with all 42 LEDs on: High / Med. / Low: 2,000 / 1,000 / 450 lx
Continuous use	ML012G: w/ BL4040, High / Med. / Low: 7 / 15 / 32 hours DML818: w/ BL1860B, High / Med. / Low: 5 / 11 / 23 hours
Dimensions (L x W x H)	ML012G: w/o Battery: 972 x 85 x 100 mm DML818: w/o Battery: 972 x 80 x 101 mm
Mounting width of Telescopic hook	1,130 - 1,900 mm
Net weight	ML012G: w/o Battery: 1.1 kg DML818: w/o Battery: 1.1 kg

**ML012G / DML818:** Battery & charger are sold separately

**Standard Equipment:** Telescopic hook (GM00002545), Hand strap (GM00002544)

The weight may differ depending on the attachment(s), including the battery cartridge. The lightest and heaviest combination, according to EPTA-Procedure 01/2014, are shown in the table. Items of standard equipment and specifications may vary by country or area. [A4-012024-1]

## CÔNG TY TNHH MAKITA VIỆT NAM

CHI NHÁNH CTY TNHH MAKITA VN TẠI MIỀN BẮC  
Khu 5, Số 1, Đường Số 6, KCN - BT - VSP, Bắc Ninh, P. Phú Châu,  
TP. Từ Sơn, T. Bắc Ninh,  
ĐT: 0222 376 5942 Fax: 0222 376 5941

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG  
CHI NHÁNH HÀ NỘI  
65 Trường Chinh, P. Phương Liệt, Q. Thanh Xuân, TP. Hà Nội,  
ĐT: 0243 202 2585

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG  
CHI NHÁNH ĐÀ NẴNG  
Số 40, Đường Chi Lăng, P. Hải Châu 1, Q. Hải Châu, TP. Đà Nẵng  
ĐT: 0236 352 5078 / 0236 352 5178 Fax: 0236 352 5479

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG  
CHI NHÁNH CẦN THƠ  
386 Võ Văn Kiệt, Khu Vực 5, P. An Thới, Q. Bình Thủy,  
TP. Cần Thơ,  
ĐT: 0292 389 4358 Fax: 0292 389 4358

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG  
CHI NHÁNH BUỒN MA THUỘT  
Số 14 Đúc Thọ, P. Thăng Kỵ, TP. Buôn Ma Thuột, T. Đắk Lắk,  
ĐT: 0262 355 4556 Fax: 0262 355 4557

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG  
CHI NHÁNH HẢI PHÒNG  
Số 01 Lô DHH1, Dự án Hoàng Huy Riverside, P. Thượng Lý,  
Q. Hồng Bàng, TP. Hải Phòng,  
ĐT: 0225 883 1529

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG  
CHI NHÁNH NHA TRANG  
Là 36/36 đường B5, Khu đô thị Vĩnh Diêm Trung, Xã Vĩnh Ngọc,  
TP. Nhà Trang, T. Khánh Hòa  
ĐT: 0258 220 0039

TRUNG TÂM DỊCH VỤ KHÁCH HÀNG  
CHI NHÁNH HỒ CHÍ MINH  
Số 12 Trịnh Văn Cấn, P. Cầu Ông Lãnh, Q. 1, TP. Hồ Chí Minh,  
ĐT: 0283 821 5191